

EHP Rapid Prototype part numbers available

| EHP Part Number | Motor | Pump | Pump Displacement (cc) |
|---------------------------|--------------|---------------------------|-------------------------------|
| EHP142BV6SGTAS20000SN0000 | GVM142-050 | Vane Pump (T7) | 20 |
| EHP142BV6SGTAS26000SN0000 | GVM142-050 | Vane Pump (T7) | 26 |
| EHP142DT6SGTAS20000SN0000 | GVM142-100 | Vane Pump (T7) | 20 |
| EHP142DT6SGTAS26000SN0000 | GVM142-100 | Vane Pump (T7) | 26 |
| EHP210BEHRGTAS20000SN0000 | GVM210-050 | Vane Pump (T7) | 20 |
| EHP210BEHRGTAS26000SN0000 | GVM210-050 | Vane Pump (T7) | 26 |
| EHP210DDDRGTBS35000SN0000 | GVM210-100 | Vane Pump (T7) | 35 |
| EHP210DDDRGTBS41000SN0000 | GVM210-100 | Vane Pump (T7) | 41 |
| EHP210DDDRGTBS50000SN0000 | GVM210-100 | Vane Pump (T7) | 50 |
| EHP210DEHRGTBS35000SN0000 | GVM210-100 | Vane Pump (T7) | 35 |
| EHP210DEHRGTBS41000SN0000 | GVM210-100 | Vane Pump (T7) | 41 |
| EHP210DEHRGTBS50000SN0000 | GVM210-100 | Vane Pump (T7) | 50 |
| EHP210FBTRGTBS35000SN0000 | GVM210-150 | Vane Pump (T7) | 35 |
| EHP210FBTRGTBS41000SN0000 | GVM210-150 | Vane Pump (T7) | 41 |
| EHP210FBTRGTBS50000SN0000 | GVM210-150 | Vane Pump (T7) | 50 |
| EHP210HCGRGTBS35000SN0000 | GVM210-200 | Vane Pump (T7) | 35 |
| EHP210HCGRGTBS41000SN0000 | GVM210-200 | Vane Pump (T7) | 41 |
| EHP210HCGRGTBS50000SN0000 | GVM210-200 | Vane Pump (T7) | 50 |
| EHP142BV6SGPG511H08UN0000 | GVM142-050 | Helical Gear Pump (PGP-H) | 8 |
| EHP142BV6SGPG511H16UN0000 | GVM142-050 | Helical Gear Pump (PGP-H) | 16 |
| EHP142BV6SGPG511H22UN0000 | GVM142-050 | Helical Gear Pump (PGP-H) | 22 |
| EHP142DT6SGPG511H08UN0000 | GVM142-100 | Helical Gear Pump (PGP-H) | 8 |
| EHP142DT6SGPG511H16UN0000 | GVM142-100 | Helical Gear Pump (PGP-H) | 16 |
| EHP142DT6SGPG511H22UN0000 | GVM142-100 | Helical Gear Pump (PGP-H) | 22 |
| EHP210BEHRGPG511H08UN0000 | GVM210-050 | Helical Gear Pump (PGP-H) | 8 |
| EHP210BEHRGPG511H16UN0000 | GVM210-050 | Helical Gear Pump (PGP-H) | 16 |
| EHP210BEHRGPG511H22UN0000 | GVM210-050 | Helical Gear Pump (PGP-H) | 22 |
| EHP210DDDRGPG517H28UN0000 | GVM210-100 | Helical Gear Pump (PGP-H) | 28 |
| EHP210DEHRGPG517H28UN0000 | GVM210-100 | Helical Gear Pump (PGP-H) | 28 |
| EHP210FBTRGPG517H28UN0000 | GVM210-150 | Helical Gear Pump (PGP-H) | 28 |
| EHP210HCGRGPG517H28UN0000 | GVM210-200 | Helical Gear Pump (PGP-H) | 28 |
| EHP210DDDRGPM028B71EN0000 | GVM210-100 | Variable Piston (P1M) | 28 |
| EHP210DDDRGPM045B71EN0000 | GVM210-100 | Variable Piston (P1M) | 45 |
| EHP210DDDRGPM054B71EN0000 | GVM210-100 | Variable Piston (P1M) | 54 |
| EHP210DEHRGPM028B71EN0000 | GVM210-100 | Variable Piston (P1M) | 28 |
| EHP210DEHRGPM045B71EN0000 | GVM210-100 | Variable Piston (P1M) | 45 |
| EHP210DEHRGPM054B71EN0000 | GVM210-100 | Variable Piston (P1M) | 54 |
| EHP210FBTRGPM028B71EN0000 | GVM210-150 | Variable Piston (P1M) | 28 |
| EHP210FBTRGPM045B71EN0000 | GVM210-150 | Variable Piston (P1M) | 45 |
| EHP210FBTRGPM054B71EN0000 | GVM210-150 | Variable Piston (P1M) | 54 |
| EHP210HCGRGPM028B71EN0000 | GVM210-200 | Variable Piston (P1M) | 28 |
| EHP210HCGRGPM045B71EN0000 | GVM210-200 | Variable Piston (P1M) | 45 |
| EHP210HCGRGPM054B71EN0000 | GVM210-200 | Variable Piston (P1M) | 54 |