



AFS Auxiliary Filtration System

Hydraulic or Gear Fluid Portable Filtration System



AFS

The AFS is the ideal way to prefilter and transfer fluids, on the ground or in the air.

Fluid should always be filtered prior to use. New fluid is not necessarily clean fluid. Most new fluids (directly from the container) are unfit for use, due to high initial contamination levels. Contamination, both particulate and water, may be introduced to a new fluid during processing, mixing, handling and storage.

The AFS uses a high capacity ModuFlow™ Plus filter for long element life and optimum filtration. The single element package provides a high level of filtration performance in a compact size. Free water is controlled by utilizing Parker's Par-Gel™ element. Par-Gel™ elements have a very high affinity for free water.

Designed with functionality, space and durability in mind the AFS comes standard with a rated lifting eye. The optimized design and rugged steel contruction allow service personnel access to the critical hydraulic systems through passageways as small as 12" x 16".

The use of a Parker portable filtration system is the most efficient and economical way to extend fluid life and protect critical system components from harmful contaminants.



Specifications:

Maximum Recommended Fluid Viscosity:

AFSG - 4080 SUS (880 cSt) 0.85 specific gravity AFSH - 500 SUS (108 cSt) 0.85 specific gravity For Optimal Particle Detector

Performance: 50-250 SUS (7.5-54 cSt)

Visual Indicator (outlet filter):

35 psid 3-band (clean, change, bypass)

Filter Bypass Valve Settings (Integral to Element):

35 psid (2.4 bar)

Operating Temperature:

-4°F to +140°F (-20°C to +60°C)

Flow Rate:

AFSG - 4 gpm (15.1 lpm) **AFSH** - 10 gpm (37.8 lpm)

Electrical Service Requried:

AFSG - 110/220 volts, 60/50 Hz, single phase, 8/4 amps **AFSH** - 110/220 volts, 60/50 Hz, single phase, 10/5 amps

Electrical Motor:

AFSG - 1/2 hp @ 1725 rpm, open, drip proof

AFSH - 3/4 hp @ 3450 rpm, open, drip proof, thermal overload protection

Construction:

Cart frame - Steel Filter head - Aluminum Filter bowl - Steel Hose - Reinforced Nitrile Wands - PVC Optional concentric wand steel

Weight: 85 lbs. (39kg)

Dimensions:

A = Height: 30.1 in (765 mm) B = Width: 15.8 in (401 mm) C = Depth: 11.9 in (960 mm)

Applications:

- Pre-clean hydraulic fluids prior to system fill
- Transferring fluid from drums or storage tanks to system reservoirs
- · Conditioning fluid in use
- Complimenting existing system filtration
- Removing free and emulsified water from a system

Features

- Visual indicator
 - Tells you when to change element
- Single filter
 - Double length filtration for long element
- Orip tray
 - Helps keep the work area safe and clean
- Smaller footprint
 - Fits into 12"x16" wind turbine hatch
- Heavy duty steel frame
 - Rugged and built to last
- 110V/220V AC motor
 - Industrial brand name
- Particle detection
 - Detects changes in contamination levels and alerts when oil is clean

- Element access cover
 - Top-accessible for easy changing of
- Hose
 - 8 foot, kink-resistant hose prevents pump cavitation

Element (not shown)

• Available for both particulate and water removal (WR)


Lifting eye (not shown)

• Rated hoist ring not to exceed 250 lbs.

Optional

Concentric wand (pg 6)

• Ready to use; no additional hardware needed



AFS - Hydraulic with IPD

Features

icountPD® - icount Particle Detector

The Most Up-to-Date Technology in Solid Particle Detection.

The design dynamics, attention to detail, and small size of the permanently mounted, on-line particle detector brings a truly innovative product to all industry. The laser based, leading-edge technology is a cost effective market solution to fluid management and contamination control.




Features and benefits of the icountPD include:

- Independent monitoring of system contamination trends.
- Early warning digital display indicators for Low, Medium and High contamination levels.
- Moisture % RH LED indicator.
- Cost effective solution in prolonging fluid life and reducing machine downtime.
- Visual indicators with power and alarm output warnings.

- Continuous performance for dependable analysis.
- Hydraulic, phosphate ester & fuel fluid compatible construction.
- Self diagnostic software.
- Fully integrated PC/PLC integration technology utilizing RS232 and 4-20mA.
- Annual calibration in US Service Center.
 Counter easily removed for return.

AFS

Replacement Parts



#	Description	AFSG	AFSH	AFSH w/ IPD	
1	Frame Assembly	946275	946275	946275	
2	Manual Motor Starter			928617	
3	Suction Hose Assmbly	946280	946280	946280	
4	Gear Pump	D22BS1A	928731	928731	
5	Electric Motor	941767	941766	941766	
6	Icount PD	PD IPD12322230			
7	Hoist Ring	945994	945994	945994	
8	Discharge tube	946281	946281	941466	
9	System 20 Sensor STI.0144.100			STI.0144.100	
10	System 20 BSP to SAE Fitting 3/8-8F40HG55				
11	Triple-Lok 37° Flare JIC Adapter 928729		928729		
12	12 Upper Discharge tube 94		946282		
13	Differential Pressure Indicator	926750	926750	926750	
14	Filter Housing	946297	946057	946057	
	Inlet/Outlet Hose *	946063	946063	946063	
	Wand Assemblies *	928624	928624	928624	
	System 20 Oil Sample Hose*			ACC6NH001	

^{*} Item not pictured


AFSOptional Parts

Concentric Wands

- Single point suction & return
- 1" diameter suction tube
- Fits openings 1.5 inches and larger
- 30" suction depth
- In-tank filtering

- One port access to the tank
- All steel construction

Standard Concentric Wand



Curved Concentric Wand



Suction Strainer Filter



AFS

How to Order

Select the desired symbol (in the correct position) to construct a model code. Example:

BOX 1	BOX 2	вох з	BOX 4	BOX 5	BOX 6	вох 7	BOX 8
AFS	Н	2	02Q	В	VP	I	1



Replacement Elements

Media	Filter (35 psid integral bypass)
02Q	937397Q
05Q	937398Q
10Q	937399Q
20Q	937400Q
WR	940734

Worldwide Filtration Manufacturing Locations

North America

Compressed Air Treatment

Gas Separation & Filtration Division

Airtek/Finite/domnick hunter/Zander Lancaster, NY 716 686 6400 www.parker.com/faf

Balston Haverhill, MA 978 858 0505

www.parker.com/balston

Engine Filtration

Racor

Modesto, CA 209 521 7860 www.parker.com/racor

Holly Springs, MS 662 252 2656 www.parker.com/racor

Hydraulic & Fuel Filtration

Hydraulic & Fuel Filtration

Metamora, OH 419 644 4311 www.parker.com/hydraulicfilter

Laval, QC Canada 450 629 9594 www.parkerfarr.com

Velcon Colorado Springs, CO 719 531 5855

www.velcon.com

Process Filtration

domnick hunter Process Filtration SciLog

Oxnard, CA 805 604 3400 www.parker.com/processfiltration

Water Purification

Village Marine, Sea Recovery, Horizon Reverse Osmosis

Carson, CA 310 637 3400 www.parker.com/watermakers

Europe

Compressed Air Treatment

domnick hunter Filtration & Separation

Gateshead, England +44 (0) 191 402 9000 www.parker.com/dhfns

Parker Gas Separations

Etten-Leur, Netherlands +31 76 508 5300 www.parker.com/dhfns

Hiross Zander

Essen, Germany +49 2054 9340 www.parker.com/hzfd

Padova, Italy +39 049 9712 111 www.parker.com/hzfd

Engine Filtration & Water Purification

Racor

Dewsbury, England +44 (0) 1924 487 000 www.parker.com/rfde

Racor Research & Development

Stuttgart, Germany +49 (0)711 7071 290-10

Hydraulic & Fuel Filtration

Hydraulic & Fuel Filtration

Arnhem, Holland +31 26 3760376 www.parker.com/hfde

Urjala, Finland +358 20 753 2500

Condition Monitoring Parker Kittiwake

West Sussex, England +44 (0) 1903 731 470 www.kittiwake.com

Process Filtration

domnick hunter Process Filtration Parker Twin Filter BV

Birtley, England +44 (0) 191 410 5121 www.parker.com/processfiltration

Asia Pacific

Australia

Castle Hill, Australia +61 2 9634 7777 www.parker.com/australia

China

Shanghai, China +86 21 5031 2525 www.parker.com/china

India

Chennai, India +91 22 4391 0700 www.parker.com/india

Parker Fowler

Bangalore, India +91 80 2783 6794 www.johnfowlerindia.com

Japan

Tokyo, Japan +81 45 870 1522 www.parker.com/japan

Korea

Hwaseon-City +82 31 359 0852 www.parker.com/korea

Singapore

Jurong Town, Singapore +65 6887 6300 www.parker.com/singapore

Thailand

Bangkok, Thailand +66 2186 7000 www.parker.com/thailand

Latin America

Parker Comercio Ltda. Filtration Division

Sao Paulo, Brazil +55 12 4009 3500 www.parker.com/br

Pan American Division

Miami, FL 305 470 8800 www.parker.com/panam

Africa

Aeroport Kempton Park, South Africa +27 11 9610700 www.parker.com/africa

© 2017 Parker Hannifin Corporation. Product names are trademarks or registered trademarks of their respective companies.





Parker Hannifin Corporation **Hydraulic & Fuel Filtration Division**16810 Fulton County Road #2

Metamora, Ohio 43540
phone 419 644 4311

www.parker.com/hydraulicfilter