



Hose Solutions

for Low Temperature Applications



ENGINEERING YOUR SUCCESS.

Hose solutions for low temperature applications up to -60°C

Parker's low temperature hoses are specially designed to work in an extremely severe cold environment, where standard hoses with a temperature range only up to -40°C are absolutely not suitable in particular in dynamic applications when the hose is moving or flexing.

Parker's low temperature hose range works safe up to -60°C and

delivers superior performances in flexibility and cold resistance. Depending on the application, our Polymer Hose Division is able to supply hoses in three different materials, whether it is rubber, thermoplastic or silicone – everything from one source.


Regarding our rubber hoses Parker is one of the few manufacturers who develops and produces his own rubber compounds.

This is the only way to create product properties which prevent cracking of rubber hoses even in extreme movement situations combined with extreme low temperatures.



Excellent service in applications up to -60°C

- General hydraulic applications
- Thermal management applications and climate control lines
- Cold chain and labs



Parker premium low temperature hoses for extremely severe cold environments

- General hydraulic rubber hoses
- General hydraulic thermoplastic hoses
- Thermal management and pharmaceutical transfer silicone hoses

General hydraulic rubber hoses

up to -57 °C

General hydraulic rubber hoses

up to -57 °C



461LT

Construction

Inner tube: Synthetic rubber
Reinforcement: Two high-tensile steel wire braids
Cover: Synthetic rubber

- No-Skive thin cover hose construction
- Excellent ozone resistance

Size: -4 up to -16
Working Pressure: 21.0 up to 42.5 MPa
Temperature: -57 up to +100 °C
Bend Radius: 75 up to 250 mm
Fitting Series: 48



SX35LT

Construction

Inner tube: Synthetic rubber
Reinforcement: Four spiral high-tensile steel wires
Cover: Synthetic rubber

- No-Skive hose construction
- Reinforcement of four high tensile steel wires
- Constant working pressure

Size: -12 up to -20
Working Pressure: 35.0 MPa
Temperature: -57 up to +100 °C
Bend Radius: 240 up to 420 mm
Fitting Series: 73 / 77



371LT

Construction

Inner tube: Synthetic rubber
Reinforcement: Three high-tensile steel wire braids
Cover: Synthetic rubber

- No-Skive hose construction - Compact Design
- Excellent ozone resistance

Size: -6 up to -16
Working Pressure: 28.0 up to 44.5 MPa
Temperature: -57 up to +100 °C
Bend Radius: 120 up to 310 mm
Fitting Series: 70



SX42LT

Construction

Inner tube: Synthetic rubber
Reinforcement: Four or six spiral high-tensile steel wires
Cover: Synthetic rubber

- No-Skive hose construction
- Reinforcement of four or six high tensile steel wires
- Constant working pressure

Size: -12 up to -20
Working Pressure: 42.0 MPa
Temperature: -57 up to +100 °C
Bend Radius: 260 up to 400 mm
Fitting Series: 73 / 77



General hydraulic thermoplast hoses

up to -57°C

Thermal management Pharmaceutical transfer silicone hoses

up to -60°C



53DM

Construction

Inner tube: Copolyester
Reinforcement: Fiber
Cover: Copolyester

**53DM
TWIN**

- High abrasion resistance
- Small bend radius
- Constant working pressure
- Excellent ozone & UV resistance

Size: -4 up to -10
Working Pressure: 21.0 MPa
Temperature: -57 up to $+100^{\circ}\text{C}$
Bend Radius: 32 up to 102 mm
Fitting Series: 56



**6722
Silicone**

Construction

Inner tube: Brick red silicone rubber compound
Reinforcement: Multiple textile plies
Cover: Blue silicon, glossy finish rubber
Size: 6 up to 25 mm
Working Pressure: 0.4 up to 0.57 MPa
Temperature: -54 up to $+177^{\circ}\text{C}$
Bend Radius: 13 – 127 mm

- Meets SAE J20 R3 Class A
- Withstand ozone and UV attack
- Weathering resistant
- Stable at extreme operating temperatures
- Chemical and oxidation resistant
- Maintains its flexibility and elasticity over time
- Good sound and vibration dampening performance
- Extended service life reducing costs
- Design factor 3:1

Applications

- Thermal management
- Trucks, buses, automobiles,
- Mobile off-road and other equipment or vehicles with heating lines.



55LT

Construction

Inner tube: Copolyester
Reinforcement: Fiber
Cover: Black copolyester, perforated

**55LT
TWIN**

- High abrasion resistance
- Small bend radius
- Excellent ozone & UV resistance

Size: -2 up to -8
Working Pressure: 14.0 up to 21.0 MPa
Temperature: -57 up to $+100^{\circ}\text{C}$
Bend Radius: 13 up to 76 mm
Fitting Series: 56



563LT

Construction

Inner tube: Copolyester
Reinforcement: Steel wire
Cover: Copolyester

Twin hose available on request

- High abrasion resistance
- Small bend radius
- Constant working pressure
- Excellent ozone & UV resistance

Size: -6 up to -10
Working Pressure: 21.0 MPa
Temperature: -57 up to $+121^{\circ}\text{C}$
Bend Radius: 64 up to 102 mm
Fitting Series: 43 / 56



Poliax

Construction

Inner tube: Translucent, smooth, phthalates free, silicone rubber compound.
Reinforcement: Plies and stainless steel wire helix
Cover: Translucent, smooth, silicone rubber compound
Size: 13 up to 51 mm
Working Pressure: 0.6 up to 1.5 MPa
Temperature: -60 up to $+200^{\circ}\text{C}$
Bend Radius: 60 – 210 mm

- Colorless (translucent) construction enables a visual inspection of the material passage
- It can be truly sterilized to ensure purity of product being manufactured or processed
- Extremely stable at elevated temperature to protect
- Low permeation to reduce or eliminate emission and odor
- Heat, ageing, ozone and abrasion resistant cover
- Design Factor 3:1 enhances safety for equipment and operators

Applications

- Pharmaceutical labs
- Medicinal ingredients
- Cosmetic ingredients
- Vacuum



594LT

Construction

Inner tube: Copolyester
Reinforcement: Steel wire
Cover: Copolyester

Twin hose available on request

- High abrasion resistance
- Small bend radius
- Constant working pressure
- Excellent ozone & UV resistance

Size: -8
Working Pressure: 28.0 MPa
Temperature: -57 up to $+100^{\circ}\text{C}$
Bend Radius: 90 mm
Fitting Series: 46

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates,
Dubai

Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, St. Florian

Tel: +43 (0)7224 66201
parker.austria@parker.com

AZ – Azerbaijan, Baku

Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/NL/LU – Benelux,

Hendrik Ido Ambacht
Tel: +31 (0)541 585 000
parker.nl@parker.com

BG – Bulgaria, Sofia

Tel: +359 2 980 1344
parker.bulgaria@parker.com

BY – Belarus, Minsk

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

CH – Switzerland, Etoy

Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany

Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst

Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup

Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid

Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa

Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve

Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Piraeus

Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budaörs

Tel: +36 23 885 470
parker.hungary@parker.com

IE – Ireland, Dublin

Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IL – Israel

Tel: +39 02 45 19 21
parker.israel@parker.com

IT – Italy, Corsico (MI)

Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty

Tel: +7 7273 561 000
parker.easteurope@parker.com

NO – Norway, Asker

Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal

Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest

Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow

Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga

Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SK – Slovakia, Banská Bystrica

Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto

Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul

Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

UK – United Kingdom, Warwick

Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park

Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario

Tel: +1 905 693 3000

US – USA, Cleveland

Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill

Tel: +61 (0)2-9634 7777

CN – China, Shanghai

Tel: +86 21 2899 5000

HK – Hong Kong

Tel: +852 2428 8008

IN – India, Mumbai

Tel: +91 22 6513 7081-85

JP – Japan, Tokyo

Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul

Tel: +82 2 559 0400

MY – Malaysia, Shah Alam

Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington

Tel: +64 9 574 1744

SG – Singapore

Tel: +65 6887 6300

TH – Thailand, Bangkok

Tel: +662 186 7000

TW – Taiwan, Taipei

Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires

Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos

Tel: +55 800 727 5374

CL – Chile, Santiago

Tel: +56 2 623 1216

MX – Mexico, Toluca

Tel: +52 72 2275 4200

EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL,
IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

US Product Information Centre

Toll-free number: 1-800-27 27 537

www.parker.com

