



AC650 Family to AC10 Substitution Guide

Electromechanical and Drives Division



ENGINEERING YOUR SUCCESS.

Parker Hannifin

AC10 Series Substitution Guide



AC650 to AC10 Part Number Conversion

220 - 240VAC / Single Phase

AC650 Part Number	AC650 Frame	AC10 Part Number	AC10 Frame	HP
650/00F3/230/SNN	1	10G-11-0015-BN	1	0.25
650/00F5/230/SNN	1	10G-11-0025-BN	1	0.5
650/00F7/230/SNN	1	10G-11-0035-BN	1	0.75
650/0001/230/SNN	1	10G-11-0045-BN	1	1
650/0002/230/SNN	2	10G-12-0070-BN	2	2

* Change last character from "N" to "F" to add Filter for both AC650V and AC10

220 - 240VAC / Three Phase

AC650 Part Number	AC650 Frame	AC10 Part Number	AC10 Frame	HP
650/0003/230/SBN	3	10G-32-0100-BN	2	3
650/0005/230/SBN	3	10G-33-0170-BN	3	5

* Change last character from "N" to "F" to add Filter for both AC650V and AC10

* All parts listed include internal brake

360 - 460VAC / Three Phase

AC650 Part Number	AC650 Frame	AC10 Part Number	AC10 Frame	HP
650/00F5/460/SNN	1	10G-41-0010-BN	1	0.5
650/00F7/460/SNN	1	10G-41-0015-BN	1	0.75
650/0001/460/SNN	1	10G-42-0020-BN	2	1
650/0002/460/SNN	2	10G-42-0040-BN	2	2
650/0003/460/SBN	2	10G-42-0065-BN	2	3
650/0005/460/SBN	2	10G-43-0090-BN	2	5
650/0007/460/SBN	3	10G-42-0120-BN	2	7.5
650/0010/460/SBN	3	10G-43-0170-BN	3	10

* Change last character from "N" to "F" to add Filter for both AC650V and AC10

* All parts listed include internal brake

Parker Hannifin

AC10 Series Substitution Guide



AC650V to AC10 Part Number Conversion

220 - 240VAC / Single Phase

AC650V Part Number	AC650V Frame	AC10 Part Number	AC10 Frame	HP
650V/00F3/230/RNN	1	10G-11-0025-BN	1	0.3
650V/00F5/230/RNN	1	10G-11-0025-BN	1	0.5
650V/00F7/230/RNN	1	10G-11-0035-BN	1	0.75
650V/0001/230/RNN	1	10G-11-0045-BN	1	1
650V/0002/230/RNN	2	10G-12-0070-BN	2	2

* AC10 0.3 HP offering is the 0.5 HP model

* Change last character from "N" to "F" to add Filter for both AC650V and AC10

220 - 240VAC / Three Phase

AC650V Part Number	AC650V Frame	AC10 Part Number	AC10 Frame	HP
650V/0003/230/RBN	3	10G-32-0100-BN	2	3
650V/0005/230/RBN	3	10G-33-0170-BN	3	5
650V/0007/230/1BN	C	10G-33-0210-BN	4	7.5
650V/0010/230/1BN	C	10G-33-0300-BN	5	10
650V/0015/230/1BN	D	10G-33-0400-BN	5	15
650V/0020/230/1BN	D	10G-33-0550-BN	6	20
650V/0025/230/1BN	D	No Available Cross	NA	25
650V/0030/230/1BN	E	No Available Cross	NA	30
650V/0040/230/CBN	F	No Available Cross	NA	40
650V/0050/230/CBN	F	No Available Cross	NA	50
650V/0060/230/CBN	F	No Available Cross	NA	60

* Change last character from "N" to "F" to add Filter, available on AC650V Frame 3 only

* Change last character from "N" to "F" to add Filter for AC10

* AC650V Units with third to last character "C" are chassis units

* Constant torque (CT) rating

* All parts listed include internal brake

* For AC650V units over 20 HP, please see the AC690+ series

Parker Hannifin

AC10 Series Substitution Guide



AC650V to AC10 Part Number Conversion

360 - 460Vac / Three Phase

AC650V Part Number	AC650V Frame	AC10 Part Number	AC10 Frame	HP
650V/00F5/460/RBN	2	10G-41-0010-BN	1	0.5
650V/00F7/460/RBN	2	10G-41-0015-BN	1	0.75
650V/0001/460/RBN	2	10G-42-0020-BN	2	1
650V/0002/460/RBN	2	10G-42-0040-BN	2	2
650V/0003/460/RBN	3	10G-42-0065-BN	2	3
650V/0005/460/RBN	3	10G-43-0090-BN	3	5
650V/0007/460/RBN	3	10G-43-0120-BN	3	7.5
650V/0010/460/RBN	3	10G-44-0170-BN	4	10
650V/0015/460/1BN	C	10G-44-0230-BN	4	15
650V/0020/460/1BN	C	10G-45-0320-BN	5	20
650V/0025/460/1BN	D	10G-45-0380-BN	5	25
650V/0030/460/1BN	D	10G-45-0440-BN	5	30
650V/0040/460/1BN	D	10G-46-0600-BN	6	40
650V/0050/460/1BN	E	10G-47-0750-BN	7	50
650V/0060/460/1BN	E	10G-47-0900-BN	7	60
650V/0075/460/CBN	F	10G-48-1100-BN	8	75
650V/0100/460/CBN	F	10G-48-1500-BN	8	100
650V/0125/460/CBN	F	10G-49-1800-BN	9	125
650V/0150/460/CBN	F	10G-49-2200-BN	9	150

* Change last character from "N" to "F" to add Filter, available on Frames 2 and 3 only

* Change last character from "N" to "F" to add Filter for AC10

* Units with third to last character "C" are chassis units. All others are IP20/NEMA 1

* Constant torque (CT) rating

* All parts listed include internal brake

Parker Hannifin

AC10 Series Substitution Guide



AC650G to AC10 Part Number Conversion

220 - 240VAC / Single Phase

AC650G Part Number	AC650G Frame	AC10 Part Number	AC10 Frame	HP
650G-21115010-B01P00-B1	1	10G-11-0025-BN	1	0.3
650G-21122010-B01P00-B1	1	10G-11-0025-BN	1	0.5
650G-21130010-B01P00-B1	1	10G-11-0035-BN	1	0.75
650G-21140010-B01P00-B1	1	10G-11-0045-BN	1	1
650G-21155020-B01P00-B1	2	10G-12-0050-BN	2	1.5
650G-21170020-B01P00-B1	2	10G-12-0070-BN	2	2
650G-21196030-B01P00-B1	3	10G-12-0100-BN	2	3

* Change first "0" after second "-" to "F" for built in EMC filter. On AC10, change "N" to "F" for filtered version.

* All parts listed include internal brake

220 - 240VAC / Three Phase

AC650G Part Number	AC650G Frame	AC10 Part Number	AC10 Frame	HP
650G-23196030-B01P00-B1	3	10G-32-0100-BN	2	3
650G-23212330-B01P00-B1	3	10G-32-0170-BN	2	4
650G-23216430-B01P00-B1	3	10G-32-0170-BN	2	5

* AC10 4 HP offering is the 5 HP model

* Change first "0" after second "-" to "F" for built in EMC filter. On AC10, change "N" to "F" for filtered version

* All parts listed include internal brake

Parker Hannifin

AC10 Series Substitution Guide



AC650G to AC10 Part Number Conversion

360 - 460VAC / Three Phase

AC650G Part Number	AC650G Frame	AC10 Part Number	AC10 Frame	HP
650G-43115020-B01P00-B1	2	10G-41-0010-BN	1	0.5
650G-43120020-B01P00-B1	2	10G-41-0015-BN	1	0.75
650G-43125020-B01P00-B1	2	10G-42-0020-BN	2	1
650G-43135020-B01P00-B1	2	10G-42-0030-BN	2	1.5
650G-43145020-B01P00-B1	2	10G-42-0040-BN	2	2
650G-43155020-B01P00-B1	2	10G-42-0065-BN	2	3
650G-43168030-B01P00-B1	3	10G-43-0090-BN	3	4
650G-43190030-B01P00-B1	3	10G-43-0090-BN	3	5
650G-43212030-B01P00-B1	3	10G-43-0120-BN	3	7.5
650G-43216030-B01P00-B1	3	10G-44-0170-BN	4	10

* AC10 4 HP offering is the 5 HP model

* Change first "0" after second "-" to "F" for built in EMC filter. On AC10, change "N" to "F" for filtered version

* All parts listed include internal brake

Parker Hannifin

AC10 Series Substitution Guide



AC650S to AC10 Part Number Conversion

220 - 240VAC / Single Phase

AC650S Part Number	AC650S Frame	AC10 Part Number	AC10 Frame	HP
650S-21115010-B01P00-A1	1	10G-11-0025-BN	1	0.3
650S-21122010-B01P00-A1	1	10G-11-0025-BN	1	0.5
650S-21130010-B01P00-A1	1	10G-11-0035-BN	1	0.75
650S-21140010-B01P00-A1	1	10G-11-0045-BN	1	1
650S-21155020-B01P00-A1	2	10G-12-0050-BN	2	1.5
650S-21170020-B01P00-A1	2	10G-12-0070-BN	2	2

*Change first "0" after second "-" to "F" for built in EMC filter. On AC10, change "N" to "F" for filtered version.

*All parts listed include internal brake

220 - 240VAC / Three Phase

AC650S Part Number	AC650S Frame	AC10 Part Number	AC10 Frame	HP
Not available	-	-	-	-

360 - 460VAC / Three Phase

AC650S Part Number	AC650S Frame	AC10 Part Number	AC10 Frame	HP
650S-43115020-B01P00-A1	2	10G-41-0010-BN	1	0.5
650S-43120020-B01P00-A1	2	10G-41-0015-BN	1	0.75
650S-43125020-B01P00-A1	2	10G-42-0020-BN	2	1
650S-43135020-B01P00-A1	2	10G-42-0030-BN	2	1.5
650S-43145020-B01P00-A1	2	10G-42-0040-BN	2	2
650S-43155020-B01P00-A1	2	10G-42-0065-BN	2	3
650S-43168030-B01P00-A1	3	10G-43-0090-BN	3	4
650S-43190030-B01P00-A1	3	10G-43-0090-BN	3	5
650S-43212030-B01P00-A1	3	10G-43-0120-BN	3	7.5
650S-43216030-B01P00-A1	3	10G-44-0170-BN	4	10

* Change first "0" after second "-" to "F" for built in EMC filter. On AC10, change "N" to "F" for filtered version

* AC10 4 HP offering is the 5 HP model

* All parts listed include internal brake

Parker Hannifin

AC10 Series Substitution Guide



When considering replacing a 650 family drive with AC10, please confirm that the mounting area available will be sufficient for the equivalent AC10.

- 1) Determine the frame size of the existing 650 family drive from the “Power Rating by Frame Size” table.
- 2) Based on the frame size, its dimensions can be retrieved from the “650 Family Dimensions by Frame Size” table.
- 3) Determine the frame size of the equivalent AC10 drive from the “Power Rating by Frame Size” table.
- 4) Based on the frame size, the AC10 dimensions are listed in the “AC10 Family Dimensions by Frame Size” table.

For your convenience, the “AC10/650 Dimensional Comparison” table shows the difference in physical size.

1 650 Family Power Rating (HP) by Frame Size

Frame	Power Rating (HP)							
	AC650		AC650G		AC650V		AC650S	
	230V	460V	230V	460V	230V	460V	230V	460V
1	.25 - 1	.5 - 1	.3 - 1	-	.3 - 1	-	.3 - 1	.5 - 1
2	2	2 - 5	1.5 - 2	.5 - 3	1.5 - 2	.5 - 2	1.5 - 2	1.5 - 3
3	3 - 5	7.5 - 10	3 - 5	4 - 10	3 - 5	3 - 10		4 - 10
C					7.5/10 - 10/15	10/15 - 20/25		
D					15/20 - 25/25	25/30 - 40/50		
E					30/40	50/60 - 60/75		
F					40/50 - 60/75	75/100 - 150		

2 650 Family Dimensions by Frame Size

Product Family	Frame	Height (in)	Width (in)	Depth (in)	Weight (lb)
650	1	5.40	2.90	5.60	2.00
650	2	7.60	2.90	6.80	3.00
650	3	10.10	3.80	7.70	6.00
650	C	13.70	7.90	8.10	20.50
650	D	17.80	9.90	9.60	38.40
650	E	26.30	10.10	12.20	71.70
650	F	28.90	10.10	13.70	90.40

Parker Hannifin

AC10 Series Substitution Guide



3 AC10 Family Power Rating (HP) by Frame Size

Product	Frame	230V	460V
AC10-IP20	1	.25 - 1	.25 - .75
	2	1.5 - 3	1 - 3
	3	5	5 - 7.5
	4	7.5	10 - 15
	5	10 - 15	20 - 30
	6	20	40
	7		50 - 60
	8		75 - 100
	9		125 - 150
	10		200
	11		225 - 250
AC10-IP66	1	.25 - 3	1 - 5
	2		7.5 - 10
	3		15 - 20
	4		25 - 40
	5		50 - 75
	6		100 - 125

4 AC10 Family Dimensions by Frame Size

Product	Frame	Height (in)	Width (in)	Depth (in)	Weight (lb)
AC10-IP20	1	5.43	3.15	5.31	2.76
	2	7.09	4.17	5.91	3.88
	3	9.25	5.43	5.98	3.88
	4	10.43	6.14	6.69	10.80
	5	13.39	8.07	7.71	16.53
	6	17.16	10.43	9.25	37.48
	7	18.90	12.40	9.21	55.12
	8	21.85	14.17	10.43	88.19
	9	24.80	16.14	11.81	121.25
	10	30.12	20.32	12.83	207.24
	11	35.83	22.05	13.46	264.56
AC10-IP66	1	16.22	7.87	7.80	15.87
	2	16.46	9.53	7.80	20.28
	3	18.54	9.53	8.98	26.90
	4	25.59	9.53	12.74	61.73
	5	26.77	12.13	14.90	85.98
	6	30.31	14.57	15.88	147.71

Parker Hannifin

AC10 Series Substitution Guide



AC650 - Size Difference

HP	230V				460V			
	Height (in)	Width (in)	Depth (in)	Weight (lb)	Height (in)	Width (in)	Depth (in)	Weight (lb)
0.25	0.03	0.25	(0.29)	0.76	AC10 Only	AC10 Only	AC10 Only	AC10 Only
0.5	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
0.75	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
1	0.03	0.25	(0.29)	0.76	1.69	1.27	0.31	1.88
2	(0.51)	1.27	(0.89)	0.88	(0.51)	1.27	(0.89)	0.88
3	(3.01)	0.37	(1.79)	(2.12)	(0.51)	1.27	(0.89)	0.88
5	(0.85)	1.63	(1.72)	(2.12)	1.65	2.53	(0.82)	0.88
7.5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.85)	1.63	(1.72)	(2.12)
10	AC10 Only	AC10 Only	AC10 Only	AC10 Only	0.33	2.34	(1.01)	4.80

Numbers in parentheses indicate negative values...ie (0.5) indicates that the AC10 is 0.5" smaller then the 650 series it is replacing.

Parker Hannifin

AC10 Series Substitution Guide



AC650V - Size Difference

HP	230V				460V			
	Height (in)	Width (in)	Depth (in)	Weight (lb)	Height (in)	Width (in)	Depth (in)	Weight (lb)
0.25 (.3 on 230V)	0.03	0.25	(0.29)	0.76	AC10 Only	AC10 Only	AC10 Only	AC10 Only
0.5	0.03	0.25	(0.29)	0.76	(2.17)	0.25	(1.49)	(0.24)
0.75	0.03	0.25	(0.29)	0.76	(2.17)	0.25	(1.49)	(0.24)
1	0.03	0.25	(0.29)	0.76	(0.51)	1.27	(0.89)	0.88
1.5	(0.51)	1.27	(0.89)	0.88	(0.51)	1.27	(0.89)	0.88
2	(0.51)	1.27	(0.89)	0.88	(0.51)	1.27	(0.89)	0.88
3 (4 also on 230V)	(3.01)	0.37	(1.79)	(2.12)	(3.01)	0.37	(1.79)	(2.12)
5	(0.85)	1.63	(1.72)	(2.12)	(0.85)	1.63	(1.72)	(2.12)
7.5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.85)	1.63	(1.72)	(2.12)
10	(0.31)	0.17	(0.39)	(3.97)	0.33	2.34	(1.01)	4.80
15	(0.31)	0.17	(0.39)	(3.97)	(3.27)	(1.76)	(1.41)	(9.70)
20	(0.64)	0.53	(0.35)	(0.92)	(0.31)	0.17	(0.39)	(3.97)
25	650V Only	650V Only	650V Only	650V Only	(0.31)	0.17	(0.39)	(3.97)
30	650V Only	650V Only	650V Only	650V Only	(4.41)	(1.83)	(1.89)	(21.87)
40	650V Only	650V Only	650V Only	650V Only	(0.64)	0.53	(0.35)	(0.92)
50	650V Only	650V Only	650V Only	650V Only	1.10	2.50	(0.39)	16.72
60	650V Only	650V Only	650V Only	650V Only	(7.40)	2.30	(2.99)	(16.58)
75	650V Only	650V Only	650V Only	650V Only	(4.45)	4.07	(1.77)	16.49
100	-	-	-	-	(7.05)	4.07	(3.27)	(2.21)
125	-	-	-	-	(4.10)	6.04	(1.89)	30.85

Numbers in parentheses indicate negative values...ie (0.5) indicates that the AC10 is 0.5" smaller then the 650 series it is replacing.

Parker Hannifin

AC10 Series Substitution Guide



AC650G - Size Difference

HP	230V				460V			
	Height (in)	Width (in)	Depth (in)	Weight (lb)	Height (in)	Width (in)	Depth (in)	Weight (lb)
0.25 (.3 @ 230V)	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
0.5	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
0.75	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
1	0.03	0.25	(0.29)	0.76	1.69	1.27	0.31	1.88
1.5	(0.51)	1.27	(0.89)	0.88	(0.51)	1.27	(0.89)	0.88
2	(0.51)	1.27	(0.89)	0.88	(0.51)	1.27	(0.89)	0.88
3 (4 also @ 230V)	(3.01)	0.37	(1.79)	(2.12)	(0.51)	1.27	(0.89)	0.88
5	(0.85)	1.63	(1.72)	(2.12)	(0.85)	1.63	(1.72)	(2.12)
7.5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.85)	1.63	(1.72)	(2.12)
10	AC10 Only	AC10 Only	AC10 Only	AC10 Only	0.33	2.34	(1.01)	4.80

* 3 HP for 650 used in chart, 4 HP moves to Frame 4 vs AC10's Frame 3

Numbers in parentheses indicate negative values...ie (0.5) indicates that the AC10 is 0.5" smaller then the 650 series it is replacing.

Parker Hannifin

AC10 Series Substitution Guide



AC650S - Size Difference

HP	230V				460V			
	Height (in)	Width (in)	Depth (in)	Weight (lb)	Height (in)	Width (in)	Depth (in)	Weight (lb)
0.25	0.03	0.25	(0.29)	0.76	AC10 Only	AC10 Only	AC10 Only	AC10 Only
0.5	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
0.75	0.03	0.25	(0.29)	0.76	0.03	0.25	(0.29)	0.76
1	0.03	0.25	(0.29)	0.76	1.69	1.27	0.31	1.88
1.5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.51)	1.27	(0.89)	0.88
2	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.51)	1.27	(0.89)	0.88
3	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.51)	1.27	(0.89)	0.88
5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.85)	1.63	(1.72)	(2.12)
7.5	AC10 Only	AC10 Only	AC10 Only	AC10 Only	(0.85)	1.63	(1.72)	(2.12)
10	AC10 Only	AC10 Only	AC10 Only	AC10 Only	0.33	2.34	(1.01)	4.80

Numbers in parentheses indicate negative values...ie (0.5) indicates that the AC10 is 0.5" smaller then the 650 series it is replacing.

Parker Hannifin

AC10 Overview

Description

AC10 Variable Frequency Drive is a simple, reliable and economical solution to every-day motor control applications requiring speed or torque control within the power range of 0.25 HP to 250 HP, with NEMA 4X indoor/IP66 version available through 20 HP. Having features normally only associated with higher specification drives, including sensorless vector mode, output frequency up to 590 Hz, UL listing, and a full 150% overload at 0.5 Hz for 1 minute, AC10 provides an optimized solution for OEM machine builders looking for a compact, cost-effective drive without compromising on performance. The AC10 is suitable for either AC induction or permanent magnet AC motor designs.

Features

Simplicity

AC10 is designed to reduce the time and effort required to install, setup and commission through its easy to use integrated keypad. Minimal wiring requirements and two easily accessed terminal rails make AC10 fast and simple to install, having you up and running in no time at all. Auto-tuning sensorless vector mode takes AC10 beyond simple V/Hz control allowing users requiring greater dynamic speed or torque control for their application to benefit from the drives enhanced 0.5% speed and 5% torque accuracy.

Reliability

Proven technology and manufacturing techniques ensure AC10 has been engineered and built to deliver consistently outstanding levels of performance day in, day out ensuring maximum uptime and productivity. Thanks to its conformally coated PC boards, AC10 is able to withstand even the most severe class 3C3 environment which many other drives in this class would struggle with, allowing you to operate AC10 with the utmost confidence in more applications. For the ultimate in protection, IP66 rated models are available.



IP20 Model



IP66 Model



Technical Characteristics - Overview

Enclosure	IP20		NEMA 4X indoor/IP66
Power Range	0.25-30 HP (0.2-22 kW)	40-250 HP (30-180 kW)	0.5-20 HP (0.4-15 kW)
Power Supply	220V - 240V ±15% Single Phase 220V - 240V ±15% Three Phase 380V - 480V +10%/-15% Three Phase		
Input Frequency	50/60 Hz		
Operating Temperature	0-40 °C		0-50 °C
Analog Inputs	2x (0-10 V, 0-5 V, 0-20 mA, 4-20 mA)		
Analog Outputs	1x (0-10 V, 0-20 mA)	2x (0-10 V, 0-20 mA)	1x (0-10 V, 0-20 mA)
Digital Inputs	5x 24 VDC	8x 24 VDC	5x 24 VDC
Digital Outputs	1x 24 VDC	2x 24 VDC	1x 24 VDC
Relay Output	1x 5 A @230 VAC		

Parker Hannifin

AC10 Ratings

Power Ratings - IP20



230V Single Phase Input				
Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
10G-11-0015-BN	0.25	0.2	1.4	1
10G-11-0025-BN	0.5	0.4	2.4	1
10G-11-0035-BN	0.75	0.55	3.3	1
10G-11-0045-BN	1	0.75	4.3	1
10G-12-0050-BN	1.5	1.1	4.8	2
10G-12-0070-BN	2	1.5	6.7	2
10G-12-0100-BN	3	2.2	9.6	2

230V Three Phase Input				
Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
10G-31-0015-BN	0.25	0.2	1.4	1
10G-31-0025-BN	0.5	0.4	2.4	1
10G-31-0035-BN	0.75	0.55	3.3	1
10G-31-0045-BN	1	0.75	4.3	1
10G-32-0050-BN	1.5	1.1	4.8	2
10G-32-0070-BN	2	1.5	6.7	2
10G-32-0100-BN	3	2.2	9.6	2
10G-33-0170-BN	5	4	17	3
10G-34-0210-BN	7.5	5.5	21	4
10G-35-0300-BN	10	7.5	30	5
10G-35-0400-BN	15	11	40	5
10G-36-0500-BN	20	15	55	6

Power Ratings - IP66



230V Three Phase Input				
Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
16G-11-0025-BN	0.5	0.4	2.4	1
16G-11-0045-BN	1	0.75	4.3	1
16G-11-0070-BN	2	1.5	6.7	1
16G-11-0100-BN	3	2.2	9.6	1

230V Three Phase Input				
Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
16G-31-0025-BN	0.5	0.4	2.4	1
16G-31-0045-BN	1	0.75	4.3	1
16G-31-0070-BN	2	1.5	6.7	1
16G-31-0100-BN	3	2.2	9.6	1

480V Three Phase Input

Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
10G-41-0006-BN	0.25	0.2	0.5	1
10G-41-0010-BN	0.5	0.4	0.9	1
10G-41-0015-BN	0.75	0.55	1.3	1
10G-42-0020-BN	1	0.75	1.7	2
10G-42-0030-BN	1.5	1.1	2.6	2
10G-42-0040-BN	2	1.5	3.5	2
10G-42-0065-BN	3	2.2	5.7	2
10G-43-0090-BN	5	4	7.8	3
10G-43-0120-BN	7.5	5.5	10	3
10G-44-0170-BN	10	7.5	15	4
10G-44-0230-BN	15	11	20	4
10G-45-0320-BN	20	15	28	5
10G-45-0380-BN	25	18.5	33	5
10G-45-0440-BN	30	22	38	5
10G-46-0600-BN	40	30	52	6
10G-47-0750-BN	50	37	65	7
10G-47-0900-BN	60	45	78	7
10G-48-1100-BN	75	55	96	8
10G-48-1500-BN	100	75	130	8
10G-49-1800-BN	125	90	157	9
10G-49-2200-BN	150	110	191	9
10G-410-2650-BN	200	132	230	10
10G-411-3200-BN	225	160	278	11
10G-411-3600-BN	250	180	313	11

480V Three Phase Input

Part Number	Nominal Power		Output Current [A]	Frame Size
	HP	kW		
16G-41-0020-BN	1	0.75	1.7	1
16G-41-0040-BN	2	1.5	3.5	1
16G-41-0065-BN	2	2.2	5.7	1
16G-41-0090-BN	5	4	7.8	1
16G-42-0120-BN	7.5	5.5	10	2
16G-42-0170-BN	10	7.5	15	2
16G-43-0230-BN	15	11	20	3
16G-43-0320-BN	20	15	28	3
16G-44-0380-BN	25	18.5	33	4
16G-44-0440-BN	30	22	38	4
16G-44-0600-BN	40	30	52	4
16G-45-0750-BN	50	37	65	5
16G-45-0900-BN	60	45	78	5
16G-45-1100-BN	75	55	96	5
16G-46-1500-BN	100	75	130	6
16G-46-1800-BN	125	90	157	6

Parker Worldwide

AE – UAE, Dubai

Tel: +971 4 8127100
parker.me@parker.com

AR – Argentina, Buenos Aires

Tel: +54 3327 44 4129

AT – Austria, Wiener Neustadt

Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt

Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AU – Australia, Castle Hill

Tel: +61 (0)2-9634 7777

AZ – Azerbaijan, Baku

Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles

Tel: +32 (0)67 280 900
parker.belgium@parker.com

BR – Brazil, Cachoeirinha RS

Tel: +55 51 3470 9144

BY – Belarus, Minsk

Tel: +375 17 209 9399
parker.belarus@parker.com

CA – Canada, Milton, Ontario

Tel: +1 905 693 3000

CH – Switzerland, Etoy

Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CL – Chile, Santiago

Tel: +56 2 623 1216

CN – China, Shanghai

Tel: +86 21 2899 5000

CZ – Czech Republic, Klecany

Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst

Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup

Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid

Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa

Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve

Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens

Tel: +30 210 933 6450
parker.greece@parker.com

HK – Hong Kong

Tel: +852 2428 8008

HU – Hungary, Budapest

Tel: +36 1 220 4155
parker.hungary@parker.com

IE – Ireland, Dublin

Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IN – India, Mumbai

Tel: +91 22 6513 7081-85

IT – Italy, Corsico (MI)

Tel: +39 02 45 19 21
parker.italy@parker.com

JP – Japan, Tokyo

Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul

Tel: +82 2 559 0400

KZ – Kazakhstan, Almaty

Tel: +7 7272 505 800
parker.easteurope@parker.com

LV – Latvia, Riga

Tel: +371 6 745 2601
parker.latvia@parker.com

MX – Mexico, Apodaca

Tel: +52 81 8156 6000

MY – Malaysia, Shah Alam

Tel: +60 3 7849 0800

NL – The Netherlands, Oldenzaal

Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Ski

Tel: +47 64 91 10 00
parker.norway@parker.com

NZ – New Zealand, Mt Wellington

Tel: +64 9 574 1744

PL – Poland, Warsaw

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira

Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest

Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow

Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga

Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SG – Singapore

Tel: +65 6887 6300

SK – Slovakia, Banská Bystrica

Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto

Tel: +386 7 337 6650
parker.slovenia@parker.com

TH – Thailand, Bangkok

Tel: +662 717 8140

TR – Turkey, Istanbul

Tel: +90 216 4997081
parker.turkey@parker.com

TW – Taiwan, Taipei

Tel: +886 2 2298 8987

UA – Ukraine, Kiev

Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick

Tel: +44 (0)1926 317 878
parker.uk@parker.com

US – USA, Cleveland

Tel: +1 216 896 3000

VE – Venezuela, Caracas

Tel: +58 212 238 5422

ZA – South Africa, Kempton Park

Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

