

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON


PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN CORP. / TUBE FITTING DIVISION
MANUFACTURERS ADDRESS: 3885 GATEWAY BLVD, COLUMBUS, OH 43228 USA
PLANT LOCATIONS: COLUMBUS TWO IN LEWISBURG

- CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY
- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
 - B Flanges: all flanges
 - C Valves: all line valves
 - D Expansion joints, flexible connections, and hose assemblies: all types
 - E Strainers, filters, separators, and steam traps
 - F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
 - G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
 - H Pressure retaining components that do not fall into one of the above categories
 - N Nuclear components: Class 1 Class 2 Class 3 (Meeting AECB or ASME requirements)



TITLE OF THE STANDARD OF CONSTRUCTION
SAE J514 AND SAE J1453
SUPPORTED BY ASME CALCULATIONS AND/OR PROOF TESTS


SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT


TYPE OF CONSTRUCTION
FORGED WELDED WROUGHT
CAST OTHER
DESCRIBE OTHER:
- COLD DRAWN BAR
- COLD FORMED

- LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:
- CATALOG
 - MATERIAL SPECIFICATIONS OR PROCESS CONTROL OVERVIEW
 - CALCULATIONS
 - IN-HOUSE TEST DATA
 - WITNESSED TEST DATA

DECLARATION:
I DIONE ARTMAN (see note 1) employed by PARKER HANNIFIN CORP and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BNY CL as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: 
Declared before me at DUBLIN, OH
This 24 day of FEBRUARY AD 2016
Commissioner of Oaths or Notary Public: (sign) 
(Affix Official seal to the right)



This space for Regulatory Authority use

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: 0A9941.5 REV2
FID#: 33

Notes:
1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

