

March 28, 2016

Attention: Scott Lehman
PARKER HANNIFIN CORPORATION
HYDRAULIC FILTER DIVISION
16810 FULTON CR2
METAMORA, OH 43540

The design submission, tracking number 2016-00383, originally received on January 20, 2016 was surveyed and accepted for registration as follows:

CRN : 0H07660.2 **Accepted on:** March 28, 2016
Reg Type: Revision To accepted Design **Expiry Date:** March 28, 2026
Drawing No. : 934141 REV D, 733456 REV G, 934005 REV F, 933936 REV H As Noted
Fitting type: HYDRAULIC FILTER HOUSING (RENEWAL)

Description	MAWP	Design Temperature	MDMT
Internal Pressure	3447kPa	38 °C	-29 °C

The registration is conditional on your compliance with the following notes:

The filter shall be hydrotested at minimum of 750 psig.

It is our understanding that the complete filter housing is constructed with aluminum casting ASTM B26 Gr.356 T6.


Please note filter housing for hydraulic fluid service is neither required nor recommended for registration because the Safety Codes Act & Regulations will apply to equipment for expansible fluid service only.

This registration is valid only for fittings fabricated at the location(s) covered by the QC certificate attached to the accepted AB-41 Statutory Declaration form. This registration is valid only until the indicated expiry date only if the Manufacturer maintains a valid quality management system approved by an acceptable third-party agency until that date. Should the approval of the quality management system lapse before the expiry date indicated above, this registration shall become void.

An invoice covering survey and registration fees will be forwarded from our Revenue Accounts.

If you have any question don't hesitate to contact me by phone at (780) 433-0281 ext 3369 or fax (780) 437-7787 or e-mail Radisavljevic@absa.ca.

Sincerely,



RADISAVLJEVIC, ZANA, R.E.T.