

**UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS**

NEW BRUNSWICK  
NUNAVUT

NOVA SCOTIA  
YUKON

PRINCE EDWARD ISLAND  
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Parker Hannifin Instrumentation Products Division	
MANUFACTURERS ADDRESS: 1005 A Cleaner Way, Huntsville, Alabama 35805	
PLANT LOCATIONS: 2651 Highway 21 North, Jacksonville, Alabama 36265	
<b>CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY</b>	
<p>A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers</p> <p>B Flanges: all flanges</p> <p>C Valves: all line valves</p> <p>D Expansion joints, flexible connections, and hose assemblies: all types</p> <p>E Strainers, filters, separators, and steam traps</p> <p>F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters</p> <p>G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs</p> <p>H Pressure retaining components that do not fall into one of the above categories</p> <p>N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/>. (Meeting CNSC or ASME requirements)</p>	TITLE OF THE STANDARD OF CONSTRUCTION MSS SP-98 Instrument Valves
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT See Attached	TYPE OF CONSTRUCTION FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER: barstock
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: Catalog 4140-R, "Parker R-max Stream Switching System" Parker R-max Stream switching System Pressure Integrity Report 2013 ISO Certificate	

**DECLARATION:**

I, Craig Beckwith (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by Det Norske Veritas as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.


Signature of Declarer: [Signature]

Declared before me at Madison County in the State of Alabama

This 10<sup>th</sup> day of October AD 2013

Commissioner of Oaths or Notary Public: (sign) [Signature]

USE THIS SPACE FOR OFFICIAL USE



This space for Regulatory Authority use

This registration must be revalidated after ten (10) years from the date of registration

CRN: OC7473.5 REV1

FID#: 1937

Notes:

- All fittings shall be registered in the name of the Manufacturer.
- Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
- The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
- Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

Northwest Territories  
**REGISTERED**  
UNDER THE AUTHORITY OF  
THE BOILER AND PRESSURE  
VESSEL ACT.  
C.R.N. OC7473.57 Rev  
SIGNED [Signature]  
DATE Dec 31 2013

53.00

Fittings Rev. 1 06/2003



Issued 6-25-79	Section IDENTIFICATION
Revised 1-15-98	Standard No. ES-703
Ecn No. ICD97055	Page 2 OF 6

Subject:  
 PRODUCT LOGO MARKING REQUIREMENTS

Parker Symbol  
 ID-3

- 1 Primary  
 Corporate Signature  
 Minimum Size 5/8"



- 2 Small Size  
 Corporate Signature  
 Maximum Size 5/8"



- 3 Linear  
 Corporate Signature



- 4 Straight Type  
 Identification—  
 Helvetica Light

Parker

- 5 Small Size "P"  
 Maximum Size 3/16"



- 6 Linear "P"



0A06793.52

- 7 Straight Type "P"  
 Identification—  
 Helvetica Light

P