

Statutory Declaration Registration of Fittings

(a) Design Qualification

I¹ Daniel R Healey
(Name of applicant)

General Manager
(Position eg, president, plant manager, chief eng.)

of Parker Canada Division
(name of company)

Located at 160 Chisholm Drive Milton, Ontario L9T 3G9
(plant address)

do solemnly declare that the fittings listed hereunder, which are subject to the Boilers & Pressure Vessels Act:

comply with all the requirements of the ANSI/ASME codes as to their dimensions, material, identification & service for which they are required:
Or

are not covered by the provisions of the ANSI/ASME codes, and are therefore constructed to comply with SAE J516 code or standard, and are designed to the best current engineering practice, as shown by the supporting test data.

(b) Quality control of Manufacture

I further declare the manufacture of these fittings is controlled by a quality control program that complies with the requirements of ISO 9001:2008 and has been verified by the following authority or authorized agency **DNV-GL**

The fittings² covered by this declaration, for which I seek registration, are Push Lok 82 Series (Catalogue 4400, February 2015)

In support of the application, the following information, calculations and/or test data are attached:
Authorized third party witness proof test report and catalogue drawings

Declared before me at _____

In the _____ of _____

This ____ day of _____ year _____
month

(A commissioner for oaths)


Signature of Declarer³

For Official Use Only

The application is accepted for registration in Category A in accordance with the Boilers and Pressure Vessels Act and CSA Standard B51.

This registration must be revalidated after ten (10) years from the date of acceptance.

Registered Number CRN **0A4396.6**

For the Chief Inspector M.L.G.
Date 07 DEC. 2015

¹ Three completed copies of the Statutory Declaration form, together with two copies of Catalogues, Drawings or Bulletins illustrating the above fittings, shall be submitted.

² All fittings are required to be registered in the name of the Manufacturer.

³ This form shall be completed and signed by the president or highest official in the manufacturing plant where the fitting is produced.

December 8, 2015

Mr. Joe Bianco
PARKER HANNIFIN CANADA INC.
4635 DURHAM RD BOX 158
GRIMSBY, ON, L3M 4G4

Type of device: PUSH LOK 82 SERIES (HOSE 1/4" - 3/4")

Manufacturer: PARKER CANADA DIVISION
160 CHISHOLM DRIVE
MILTON, ON, L9T3G9

Dear Sir,

According to our law respecting pressure vessels, your design has been reviewed and registered as follows:

CRN N°: 0A4396.6

Our reference No: 957178

Main Design No. : CATALOGUE 4400, FEBRUARY 2015

Note: If the CRN is a five digit number following the letter and start with a 0, the 0 is not considered to be an integral part of the CRN.

Yours truly,

TS for

Maricel Lascarache

Inspecteur autorisé (e)
Direction de l'inspection de la fabrication
d'appareils sous pression