

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR


MANUFACTURERS NAME: Parker Hannifin Instrumentation Products Division	
MANUFACTURERS ADDRESS: 1005 A Cleaver Way, Huntsville, Alabama	
PLANT LOCATIONS: 301 Wagner Drive, Boaz, Alabama	
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY <input checked="" type="checkbox"/> A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers <input type="checkbox"/> B Flanges: all flanges <input type="checkbox"/> C Valves: all line valves <input type="checkbox"/> D Expansion joints, flexible connections, and hose assemblies: all types <input type="checkbox"/> E Strainers, filters, separators, and steam traps <input type="checkbox"/> F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters <input type="checkbox"/> G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs <input type="checkbox"/> H Pressure retaining components that do not fall into one of the above categories <input type="checkbox"/> N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting CNSC or ASME requirements)	
TITLE OF THE STANDARD OF CONSTRUCTION ASME B 31.1, B31.3 (see catalog)	
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT See attached examples of acceptable marking <div style="text-align: center; font-size: 2em; font-family: cursive;">see attached</div>	
TYPE OF CONSTRUCTION FORGED <input checked="" type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input type="checkbox"/> CAST <input type="checkbox"/> OTHER <input checked="" type="checkbox"/> DESCRIBE OTHER: BAR STOCK	
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: Catalog 4280, dated May 2014, "Instrumentation Pipe & ISO Conversion Fittings", Catalog 4280, dated November 2001, "Welded Fittings", Scope of Registration Renewal OA2205.6	

DECLARATION:

I, Tony Wyszowski (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by Dot Norske Veritas as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]
 Declared before me at Huntsville in the state of Alabama
 This 20th day of November AD 2014
 Commissioner of Oaths or Notary Public: (sign) [Signature]

USE THIS SPACE FOR OFFICIAL



This space for Regulatory Authority use
 This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OA2205.5 REV2
 FID#: 1937

Notes:
 1. All fittings shall be registered in the name of the Manufacturer.
 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

Northwest Territories
REGISTERED
 UNDER THE AUTHORITY OF
 THE BOILER AND PRESSURE
 VESSEL ACT.
 C.R.N. OA2205.5 REV2
 SIGNED [Signature]
 DATE Feb 20 2015 (Rev. 1 06/2003)

A 5300