

**UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS**

NEW BRUNSWICK  
NUNAVUT

NOVA SCOTIA  
YUKON

PRINCE EDWARD ISLAND  
NORTHWEST TERRITORIES


NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER CANADA DIVISION.  
 MANUFACTURERS ADDRESS: 160 CHISHOLM DRIVE MILTON ONT. L9T 3G9  
 PLANT LOCATIONS: AS PER ISO DOCUMENT PAGE 2.

- CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY**
- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
  - B Flanges: all flanges
  - C Valves: all line valves
  - D Expansion joints, flexible connections, and hose assemblies: all types
  - E Strainers, filters, separators, and steam traps
  - F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
  - G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
  - H Pressure retaining components that do not fall into one of the above categories
  - N Nuclear components: Class 1  Class 2  Class 3  (Meeting AECB or ASME requirements)

**TITLE OF THE STANDARD OF CONSTRUCTION**  
MANUFACTURER'S STANDARD SUPPORTED BY PROOF TEST REPORTS.

**SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT**





**TYPE OF CONSTRUCTION**

FORGED  WELDED  WROUGHT   
 CAST  OTHER   
 DESCRIBE OTHER: FITTINGS ARE MACHINED FROM BRASS STEEL AND STAINLESS STEEL.

- LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:**
- CATALOG 4660 PAGES A68 TO A76 AND E65 TO E90
  - PROOF TEST REPORT (PER ARPM HOSE HANDBOOK) AND SCOPE OF REGISTRATION

**DECLARATION:**  
 I DANIEL R. HEALEY (see note 3) employed by PARKER CANADA and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by DNV-GL as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer:   
 Declared before me at Milton, Ontario  
 This 9 day of January AD 2017  
 Commissioner of Oaths or Notary Public: (sign)   
 (Affix Official seal to the right)

USE THIS SPACE FOR THE OFFICIAL SEAL


This space for Regulatory Authority use  
 This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: CSA - OD10154.56R2  
 A. BANWAT I  
 MARCH 28 2017

**REGISTERED**  
 CRN: CSA - OD10154.56R2  
 Registration Process administered by CSA Group per CSA B51

Notes:  
 1. All fittings shall be registered in the name of the Manufacturer.  
 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.  
 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.  
 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

Expiry date: DEC. 05. 2026

 Note: 1. This registration is based on CSA B51 reciprocal policy.  
 2. See attachment as the scope of registration.  
 3. Base on the burst testing results, model 950B size 12 & 16 MAWP shall be reduced to 3375 psi @ 73 °F.