



LSHT MOTOR WI-MK072

HYDRAULIC

▶▶ EXPRESS PROGRAM



ENGINEERING YOUR SUCCESS.

TB SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TB0050FS100AAAB	3.0 / 49	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0050AS100AAAB	3.0 / 49	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0065FS100AAAB	4.0 / 65	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0065AS100AAAB	4.0 / 65	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0080FS100AAAB	5.0 / 82	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0080AS100AAAB	5.0 / 82	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0100FS100AAAB	6.0 / 98	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0100AS100AAAB	6.0 / 98	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0130FS100AAAB	8.0 / 130	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0130AS100AAAB	8.0 / 130	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0165FS100AAAB	10.0 / 163	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0165AS100AAAB	10.0 / 163	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0195FS100AAAB	11.9 / 195	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0195AS100AAAB	11.9 / 195	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0230FS100AAAB	13.9 / 228	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0230AS100AAAB	13.9 / 228	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0260FS100AAAB	15.9 / 260	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0260AS100AAAB	15.9 / 260	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0295FS100AAAB	17.9 / 293	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0295AS100AAAB	17.9 / 293	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0330FS100AAAB	20.0 / 328	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0330AS100AAAB	20.0 / 328	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0365FS100AAAB	22.6 / 370	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0365AS100AAAB	22.6 / 370	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0390FS100AAAB	24.0 / 392	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TB0390AS100AAAB	24.0 / 392	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT

- **PART NUMBERS ON THIS PAGE ARE PART OF STOCKING PROGRAM**
- 3 CUBIC INCH – 24 CUBIC INCH DISPLACEMENTS
- 2 BOLT & 4 BOLT MOUNT
- 1" KEYED SHAFT
- SAE PORTING
- UNPAINTED



TE SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TE0045FS100AAAB	2.5 / 41	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0045AS100AAAB	2.5 / 41	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0050FS100AAAB	3.0 / 49	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0050AS100AAAB	3.0 / 49	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0065FS100AAAB	4.0 / 65	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0065AS100AAAB	4.0 / 65	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0080FS100AAAB	5.0 / 82	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0080AS100AAAB	5.0 / 82	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0100FS100AAAB	6.0 / 98	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0100AS100AAAB	6.0 / 98	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0130FS100AAAB	8.0 / 130	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0130AS100AAAB	8.0 / 130	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0165FS100AAAB	10.0 / 163	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0165AS100AAAB	10.0 / 163	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0195FS100AAAB	11.9 / 195	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0195AS100AAAB	11.9 / 195	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0230FS100AAAB	13.9 / 228	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0230AS100AAAB	13.9 / 228	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0295FS100AAAB	17.9 / 293	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0295AS100AAAB	17.9 / 293	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0330FS100AAAB	20.0 / 328	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0330AS100AAAB	20.0 / 328	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0390FS100AAAB	24.0/392	4 BOLT	7/8-14 SAE	1" KEYED	NO PAINT
TE0390AS100AAAB	24.0/392	2 BOLT	7/8-14 SAE	1" KEYED	NO PAINT

- **PART NUMBERS ON THIS PAGE ARE PART OF STOCKING PROGRAM**
- 2.5 CUBIC INCH – 24 CUBIC INCH DISPLACEMENTS
- 2 BOLT & 4 BOLT MOUNT
- 1" KEYED SHAFT
- SAE PORTING
- UNPAINTED



TF SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TF0170MS030AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0170MS050AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0195MS030AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0195MS050AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0240MS030AAAB	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0240MS050AAAB	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0280MS030AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0280MS050AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0360MS030AAAB	22.2 / 364	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0360MS050AAAB	22.2 / 364	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0405MS030AAAB	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0405MS050AAAB	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0475MS030AAAB	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TF0475MS050AAAB	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT

- **PART NUMBERS ON THIS PAGE ARE PART OF STOCKING PROGRAM**
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- TF SERIES - 11.9 CUBIC INCH – 29.1 CUBIC INCH DISPLACEMENTS
- MAGNETO MOUNT
- STD 1.25" KEYED & 1.25" SPLINED SHAFTS
- SAE PORTING
- UNPAINTED



TG SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TG0140MS030AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0140MS050AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0170MS030AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0170MS050AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0195MS030AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0195MS050AAAB	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0240MS030AAAB	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0240MS050AAAB	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0280MS030AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0280MS050AAAB	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0335MS030AAAB	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0335MS050AAAB	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0405MS030AAAB	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0405MS050AAAB	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0475MS030AAAB	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0475MS050AAAB	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0530MS030AAAB	32.3 / 528	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0530MS050AAAB	32.3 / 528	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0625MS030AAAB	38.0 / 623	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0625MS050AAAB	38.0 / 623	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0785MS030AAAB	48.0 / 786	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0785MS050AAAB	48.0 / 786	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT

- **PART NUMBERS ON THIS PAGE ARE PART OF STOCKING PROGRAM**
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- TG SERIES – 11.9 CUBIC INCH – 48.0 CUBIC INCH DISPLACEMENTS
- MAGNETO MOUNT
- STD 1.25" KEYED & 1.25" SPLINED SHAFTS
- SAE PORTING
- UNPAINTED



TK SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TK0250K5320AAAB	15.3 / 250	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0250K5360AAAB	15.3 / 250	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK0315K5320AAAB	19.2 / 315	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0315K5360AAAB	19.2 / 315	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK0400K5320AAAB	24.4 / 400	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0400K5360AAAB	24.4 / 400	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK0500K5320AAAB	30.5 / 500	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0500K5360AAAB	30.5 / 500	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK0630K5320AAAB	38.4 / 630	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0630K5360AAAB	38.4 / 630	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK0800K5320AAAB	48.8 / 800	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK0800K5360AAAB	48.8 / 800	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL
TK1000K5320AAAB	61.0 / 1000	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	NO PAINT, PORTS - REAR RADIAL
TK1000K5360AAAB	61.0 / 1000	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	NO PAINT, PORTS - REAR RADIAL

- **PART NUMBERS ON THIS PAGE ARE PART OF STOCKING PROGRAM**
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- TK SERIES – 15.3 CUBIC INCH – 61.0 CUBIC INCH DISPLACEMENTS
- SAE CC 4 BOLT MOUNT
- 1.5" KEYED & 1.5" SPLINED SHAFTS
- SAE PORTING, REAR RADIAL
- UNPAINTED



TF SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TF0080MS030AAAA	4.9 / 81	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0080MS030AAAB	4.9 / 81	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0080MS050AAAA	4.9 / 81	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0080MS050AAAB	4.9 / 81	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0100MS030AAAA	6.1 / 100	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0100MS030AAAB	6.1 / 100	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0100MS050AAAA	6.1 / 100	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0100MS050AAAB	6.1 / 100	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0130MS030AAAA	7.8 / 128	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0130MS030AAAB	7.8 / 128	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0130MS050AAAA	7.8 / 128	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0130MS050AAAB	7.8 / 128	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TF0170MS030AAAA	10.3 / 169	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0170MS050AAAA	10.3 / 169	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0195MS030AAAA	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0195MS050AAAA	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TF0240MS030AAAA	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0240MS050AAAA	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TF0280MS030AAAA	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0280MS050AAAA	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TF0360MS030AAAA	22.2 / 364	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0360MS050AAAA	21.2 / 364	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TF0405MS030AAAA	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0405MS050AAAA	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TF0475MS030AAAA	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TF0475MS050AAAA	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT

- PART NUMBERS ON THIS PAGE ARE **NOT** PART OF STOCKING PROGRAM
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- 10 DAY FACTORY LEAD TIME
- TF SERIES - 4.9 CUBIC INCH – 29.1 CUBIC INCH DISPLACEMENTS
- MAGNETO MOUNT
- STD 1.25" KEYED & 1.25" SPLINED SHAFTS
- SAE PORTING
- PAINTED & UNPAINTED



TG SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TG0140MS030AAAA	8.6 / 141	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0140MS050AAAA	8.6 / 141	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0170MS030AAAA	10.3 / 169	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0170MS050AAAA	10.3 / 169	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0195MS030AAAA	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0195MS050AAAA	11.9 / 197	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0240MS030AAAA	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0240MS050AAAA	14.5 / 238	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0280MS030AAAA	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0280MS050AAAA	17.1 / 280	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0310MS030AAAA	18.9 / 310	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0310MS030AAAB	18.9 / 310	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0310MS050AAAA	18.9 / 310	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0310MS050AAAB	18.9 / 310	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT
TG0335MS030AAAA	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0335MS050AAAA	20.6 / 337	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0405MS030AAAA	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0405MS050AAAA	24.7 / 405	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0475MS030AAAA	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0475MS050AAAA	29.1 / 477	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0530MS030AAAA	32.3 / 528	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0530MS050AAAA	32.3 / 528	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0625MS030AAAA	38.0 / 623	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0625MS050AAAA	38.0 / 623	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0785MS030AAAA	48.0 / 786	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0785MS050AAAA	48.0 / 786	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0960MS030AAAA	58.5 / 959	MAGNETO	7/8-14 SAE	1.25" KEYED	BLACK PAINT
TG0960MS030AAAB	58.5 / 959	MAGNETO	7/8-14 SAE	1.25" KEYED	NO PAINT
TG0960MS050AAAA	58.5 / 959	MAGNETO	7/8-14 SAE	1.25" SPLINE	BLACK PAINT
TG0960MS050AAAB	58.5 / 959	MAGNETO	7/8-14 SAE	1.25" SPLINE	NO PAINT

- PART NUMBERS ON THIS PAGE ARE **NOT** PART OF STOCKING PROGRAM
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- 10 DAY FACTORY LEAD TIME
- 8.6 CUBIC INCH – 58.5 CUBIC INCH DISPLACEMENTS
- MAGNETO MOUNT
- STD 1.25" KEYED & 1.25" SPLINED SHAFTS
- SAE PORTING
- PAINTED & UNPAINTED



TK SERIES LSHT MOTORS					
PART NUMBER	CU.IN / CC	MOUNT	PORTS	SHAFT	OPTIONS
TK0250K5320AAAA	15.3 / 250	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0250K5360AAAA	15.3 / 250	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK0315K5320AAAA	19.2 / 315	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0315K5360AAAA	19.2 / 315	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK0400K5320AAAA	24.4 / 400	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0400K5360AAAA	24.4 / 400	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK0500K5320AAAA	30.5 / 500	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0500K5360AAAA	30.5 / 500	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK0630K5320AAAA	38.4 / 630	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0630K5360AAAA	38.4 / 630	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK0800K5320AAAA	48.8 / 800	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK0800K5360AAAA	48.8 / 800	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL
TK1000K5320AAAA	61.0 / 1000	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" KEYED	BLACK PAINT, PORTS - REAR RADIAL
TK1000K5360AAAA	61.0 / 1000	SAE CC , 4 BOLT	1 5/16-12 SAE	1.5" SPLINE	BLACK PAINT, PORTS - REAR RADIAL

- PART NUMBERS ON THIS PAGE ARE **NOT** PART OF STOCKING PROGRAM
- **SPECIAL PRICING APPLIES PER MASTER QUOTE**
- 10 DAY FACTORY LEAD TIME
- 15.3 CUBIC INCH – 61.0 CUBIC INCH DISPLACEMENTS
- SAE CC 4 BOLT MOUNT
- STD 1.5" KEYED & 1.5" SPLINED SHAFTS
- SAE PORTING, REAR RADIAL
- PAINTED



(Restricted for use by Parker Hannifin Personnel and Authorized Distributors) © 2015 Parker Hannifin Corporation



Parker Canada Division

Milton (905) 693-3000
Montreal (514) 684-3000
Calgary (403) 291-9284

pcdmktg@parker.com

Parker Policy MI-WK072

Confidential
Effective Date: February 1ST 2017
Issue Date:
Supersedes: N/A

www.parker.com/hbuexpress