


**UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS**

NEW BRUNSWICK                      NOVA SCOTIA                      PRINCE EDWARD ISLAND                      NEWFOUNDLAND AND LABRADOR  
 NUNAVUT                              YUKON                              NORTHWEST TERRITORIES

MANUFACTURERS NAME: Parker Hannifin Manufacturing Ltd, domnick hunter filtration and separation division	
MANUFACTURERS ADDRESS: Dukesway, Team Valley Trading Estate, Gateshead, Tyne and Wear, NE11 0PZ, UK	
PLANT LOCATIONS: Dukesway, Team Valley Trading Estate, Gateshead, Tyne and Wear, NE11 0PZ, UK	
<b>CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY</b>	
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges C Valves: all line valves D Expansion joints, flexible connections, and hose assemblies: all types <input checked="" type="checkbox"/> E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> . (Meeting CNSC or ASME requirements)	<b>TITLE OF THE STANDARD OF CONSTRUCTION</b> Proprietary design supported by ASME design calculations
<b>SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT</b>	
	
<b>TYPE OF CONSTRUCTION</b>	
FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER: Bolted Aluminium Extrusion	
<b>LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:</b>	
Exhibit A: Uniform Statutory Declaration Exhibit B: Support Sales Literature Exhibit C: Specification and Detail Drawings Exhibit D: Design Calculations Exhibit E: Material Certificates Exhibit F: Lloyd's Design Appraisal Documents Exhibit G: Quality System Certificate	

**DECLARATION:**

I, Derek Bankler (see note 3) employed by Parker Hannifin Manufacturing and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by Lloyd's Register Quality Assurance as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]  
 Declared before me at Gateshead  
 This 19th day of August 2004  
 Commissioner of Oaths or Notary Public: (sign) James Bowyer LLB

U S E  
 James Bowyer LL.B.  
 Notary Public  
 OF 77 West Road  
 Newcastle upon Tyne  
 NE15 6PR  
 Tel: 07860 725169

This space for Regulatory Authority Use

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OH9672.5 REV1  
 FID#: 484

Notes:  
 1. All fittings shall be registered in the name of the Manufacturer.  
 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.  
 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.  
 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

Sect. 1.0 - Fittings Rev. 1 06/2003

