

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick
Nunavut

Nova Scotia
Yukon

Prince Edward Island
Northwest Territories

Newfoundland and Labrador

Manufacturers Name: Parker Hannifin Manufacturing Ltd	
Manufacturers Address: Dukesway, Team Valley Trading Estate, Gateshead, Tyne & Wear, NE11 0PZ, England	
Plant Locations: "as manufactures address"	
<p>Category of Fittings to be registered. Circle one Category only</p> <p>A- Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps or reducers</p> <p>B- Flanges, all flanges</p> <p>C- Valves, all line valves</p> <p>D- Expansion joints, flexible connections, and hose assemblies, all types</p> <p>E- Strainers, filters, separators, and steam traps</p> <p>F- Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters</p> <p>G- Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs</p> <p>H- Pressure retaining components that do not fall into one of the above categories</p> <p>I- Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> Meeting CNSC or ASME requirements</p>	<p align="center">Title of the Standard of Construction</p> <p align="center">CATEGORY "E"</p> <p>"this is a 10 year renewal for OE11278.2C"</p> <p>(already approved by TSSA)</p>
<p>Show Manufacturers Name, Trademark or Logo as it will appear on the product</p>	<p align="center">Type of Construction</p> <p>Forged <input type="checkbox"/> Welded <input type="checkbox"/> Wrought <input type="checkbox"/></p> <p>Cast <input checked="" type="checkbox"/> Other <input type="checkbox"/></p> <p>Describe other:</p>
<p>List of supporting documentation and identification of the actual items to be registered:</p> <p>Full Original Report and update ISO certificates, Uniform Statutory Declaration, Sales Support Literature, Specification & Detail Drawings, Design Calculations, materials, Quality System Certificate etc</p>	

Declaration:

I Derek Simpson (see note 3) employed by Parker Hannifin Manufacturing Ltd and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by Lloyds (ISO 9000 : 2015) as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer:

Declared before me at _____

This _____ day of _____ AD _____

Commissioner of Oaths

Or Notary Public: (sign) _____

Use this space for Official Seal

(Affix Official seal to the right)

This space for Regulatory Authority use.

CRN: OE11278.2 Rev2

FD#: 15469

Revision is CRN renewal. Oil-X, GL2, -3, -5, -7, -9.

- Notes:
1. All Fittings shall be registered in the name of the Manufacturer.
 2. Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
 3. The Declaration shall be made by the person having full authority and responsibility for the quality of the end product.
 4. Quality Control programs shall be resubmitted for validation.
- water separators. 300psi @ -4F to 212F; 1/4" to 3"
- 11/2016 BSP/NPT; CRN expires Jan.20, 2031 - DG

