



345 Carlingview Drive  
Toronto, Ontario M9W 6N9  
Tel.: 416.734.3300  
Fax: 416.231.1626  
Toll Free: 1.877.682.8772

[www.tssa.org](http://www.tssa.org)

May 6, 2021

PRESSURE VESSEL ENGINEERING LTD.  
120 RANDALL DR SUITE B  
WATERLOO ON N2V 1C6

**Workorder Type:** Registration - Fitting(Conventional)  
**Workorder No:** SR3014672  
**Your Reference No.:** 15877  
**Registered to:** PARKER HANNIFIN CORPORATION QUICK COUPLING DIVISION

Dear CATHERINE DIPLOCK,

Technical Standards and Safety Authority (TSSA) is pleased to inform you that your submission has been reviewed and registered as follows:

CRN : 0H21191.25  
Main Design No.: Series 60 Quick Connect Fittings per Scope of Registration Document: 15877s-1 R0  
Expiry Date: Jan 17, 2031

Please be advised that a valid quality control system must be maintained for the fitting registration to remain valid until the expiry date.

The stamped copy of the approved registration and the invoice are mailed separately (There will be no hard copies for electronic submissions). Should you have any questions or require further assistance, please contact a Customer Service Advisor at 1.877.682.TSSA (8772) or e-mail [customerservices@tssa.org](mailto:customerservices@tssa.org). We will be happy to assist you. When contacting TSSA regarding this file, please refer to the Service Request number provided above.

Yours truly,

Zivko Gacevic ,P. Eng.  
Engineer, BPV  
Tel. : +1 416-734-3429  
Email : [zgacevic@tssa.org](mailto:zgacevic@tssa.org)



Technical Standards and Safety Authority  
 345 Carlingview Drive  
 Toronto, Ontario M9W 6N9  
 www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



## STATUTORY DECLARATION Registration of Fittings

I, Paul Lemay Engineering Manager  
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Parker Hannifin Corporation Quick Coupling - US Division  
(Name of Manufacturer)

Located at 8145 Lewis Road, Golden Valley, MN, 55345 USA  
(Plant Address) (Telephone No.) (Fax No.)

do solemnly declare that the fittings listed hereunder, which are subject to the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, comply with all of the requirements of

(Title of recognized North American Standard)

which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with ASME B31.3 2018ED as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO9001:2015 which has been verified by the following authority, Bureau Veritas


The items covered by this declaration, for which I seek registration, are category \_\_\_\_\_ type fittings. In support of this application, the following information and/or test data are attached as follows:

See Scope Document: 15877s-1 R0  
(drawings, calculations, test reports, etc.)

Declared before me at Golden Valley in the STATE of MINNESOTA  
 the 19<sup>th</sup> day of November AD 2020.

Commissioner for Oaths:

Kurtis M Krause  
(Printed name)



[Signature]  
(Signature)

[Signature]  
(Signature of Declarer)

### FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category 'H'.

CRN: \_\_\_\_\_

Registered by: \_\_\_\_\_

Dated: \_\_\_\_\_

**NOTE: This registration expires on: Jan. 17, 2031**

**Technical Standards and Safety Authority**      **Boilers and Pressure Vessels Safety Program**

**REGISTERED**

C.R.N.: 0H21191.25

Signed: [Signature]

Date: May 6, 2021.



Document: 15877s-1 R0

Date: December 17, 2020

**Scope of Registration: Series 60 Quick Connect fittings.**

**Design Data:**

Design Code: ASME B31.3 2018ED

MAWP: See below

MDMT: -320°F

Hydrotest: 1.5x MAWP

Impact Testing: Exempt per 323.2.2

Corrosion Allowance: none

**Drawings Included:**

- SSH1-62Y & SSH1-63Y
  - o MAWP: 2000 psi @ 100°F
- SSH2-62Y & SSH2-63Y
  - o MAWP: 2000 psi @ 100°F
- SSH3-62Y & SSH3-63Y
  - o MAWP: 1500 psi @ 100°F
- SSH4-62Y & SSH4-63Y
  - o MAWP: 1500 psi @ 100°F
- SSH6-62Y & SSH6-63Y
  - o MAWP: 1500 psi @ 100°F
- SSH8-62Y & SSH8-63Y
  - o MAWP: 1000 psi @ 100°F
- SSH12-62NY & SSH12-63NY
  - o MAWP: 1000 psi @ 100°F
- SSH2016-62Y & SSH2016-63Y
  - o MAWP: 1000 psi @ 100°F
- SSH2024-62Y & SSH2024-63Y [Same design as SSH2016]
  - o MAWP: 1000 psi @ 100°F

**THIS IS PART OF CRN**  
**0H21191.25**  
Technical Standards and Safety Authority  
Boilers and Pressure Vessels Safety  
Program

**Validation:**

- Burst Test Report: PVE\_Report 20010547
- UG-101 calculations: 15877c-1 R0