




TECHNICAL STANDARDS & SAFETY AUTHORITY
 14th Floor, Centre Tower
 3300 Bloor Street West
 Toronto, Ontario
 Canada M8X 2X4



STATUTORY DECLARATION Registration of Fittings

I, Diane Artman, Division Engineering Manager
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Parker Hannifin Corporation / Tube Fitting Division
(Name of Manufacturer)

Located at 3885 Gateway Blvd, Columbus, OH 43228, USA 614-279-7070 614-279-7685
(Plant Address) (Telephone No.) (Fax No.)

do solemnly declare that the fittings listed hereunder, which are subject to the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, comply with all of the requirements of

(Title of recognized North American Standard)
 which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with SAE J514 and J1453 as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2008 which has been verified by the following authority, DNV GL.

The items covered by this declaration, for which I seek registration, are category A type fittings. In support of this application, the following information and/or test data are attached as follows:
Fittings per attached list from Catalog 4300 - December 2011

(drawings, calculations, test reports, etc.)

Declared before me at Dublin in the state of Ohio
 the 29th day of April AD 20 16.

Commissioner for Oaths:

Kristina A. Chandler
(Printed name)

Kristina A. Chandler
(Signature)

[Handwritten Signature]

(Signature of Declarer)



FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category A.

CRN: QA9941.54

Registered by: RYAN ORCESKI

Dated: JAN 25, 2016



NOTE: This registration expires on: MAY 4, 2026

Plant Locations

Division Headquarters
3885 Gateway Boulevard
Columbus, OH 43228 USA

725 North Beech Street
Eaton, OH 45320 USA

700 West Cumberland Street
Lewisburg, OH 45338 USA

704 West Cumberland Street
Lewisburg, OH 45338 USA

Am Metallwerk 9
33659 Bielefeld
Germany

Bahndamm 31 - 33
33758 Schlob Holte-Stukenbrock
Germany

Sp.z o.o.
ul. E. Kwiatkowskiego 16
55-011 Siechnice
Poland

Antiguo Camino a San Lorenzo No. 338
50010
Toluca, Mexico

No. 233 Yuejin Road
Lane 655
Baoan Highway
Shanghai 201906, P. R. China
Shanghai, China



Fitting series: Feruok Flareless SAE J514, catalog section C

Material: steel and stainless steel when available

| Part Number | Size Range | Comparable Fittings | Mating Components |
|-------------|--------------|---------------------|-------------------|
| HBU | 2 TO 32 | F5BU | FNU, C6BU |
| LHBU | 2 TO 32 | F5BU | FNU, C6BU |
| F5BU | 2 TO 32 | | FNU, C6BU |
| WBU | 4 TO 32 | F5BU, HBU | FNU, C6BU |
| FBU | 2 TO 32 | | FNU, C6BU, HPC |
| GBU | 2 TO 32 | | FNU, C6BU, HP |
| V5BU | 4 TO 32 | C5BU | FNU, C6BU |
| TRBU | 6-4 TO 24-20 | HBU | FNU, C6BU |
| VBU | 3 TO 32 | CBU | FNU, C6BU, HPC |
| EBU | 2 TO 32 | C5BU | FNU, C6BU, HPC |
| C6BU | 2 TO 32 | | PNU, F5BU |
| WEBU | 2 TO 32 | EBU | FNU, C6BU |
| C5BU | 3 TO 32 | | FNU, C6BU |
| CC5BU | 4 TO 32 | C5BU | FNU, C6BU |
| DBU | 4 TO 32 | | FNU, C6BU, HP |
| CBU | 2 TO 32 | | FNU, C6BU, HPC |
| JBU | 2 TO 32 | EBU | FNU, C6BU |
| R6BU | 4 TO 32 | C6BU | PNU, F5BU |
| S6BU | 4 TO 32 | C6BU | PNU, F5BU |
| S5BU | 4 TO 32 | C5BU | FNU, C6BU |
| R5BU | 4 TO 32 | C5BU | FNU, C6BU |
| RBU | 4 TO 32 | CBU | FNU, C6BU, HPC |
| SBU | 4 TO 32 | CBU | FNU, C6BU, HPC |
| OBU | 4 TO 32 | DBU | FNU, C6BU, HP |
| MBU | 4 TO 32 | DBU | FNU, C6BU, HP |
| PNU | 2 TO 24 | HBU | C6BU |
| KBU | 4 TO 32 | EBU | FNU, C6BU |
| BU | 2 TO 32 | HBU | TU, TUBE |
| TU | 2 TO 32 | HBU | BU, TUBE |
| FNU | 2 TO 24 | HBU | F5BU |

NOTE:

Unless otherwise indicated in Parker catalog 4300, stainless steel fittings have same pressure ratings as carbon steel

